

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P170432

Luminaire Tested: **LDA4A09840D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P170432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A09840D010TE LAR25NF 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 966.2 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P170432
CATALOG NUMBER: LDA4A09840D010TE LAR25NF 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P170432

CATALOG NUMBER: LDA4A09840D010TE LAR25NF 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83
7	97	90	86	83	95	90	86	83	89	85	83	88	85	82	87	84	82	81
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538342
5°	471903
10°	351973
15°	223904
20°	118739
25°	26797
30°	6438
35°	1852
40°	628
45°	192
50°	115
55°	129
60°	148
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P170432

CATALOG NUMBER: LDA4A09840D010TE LAR25NF 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.4	34.5
10°-20°	479.0	49.6
20°-30°	141.7	14.7
30°-40°	10.1	1.0
40°-50°	1.2	0.1
50°-60°	0.5	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.1	98.7
0°-40°	964.2	99.8
0°-60°	965.9	100.0
0°-90°	966.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	966.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4364	
5°	3811	333
15°	1753	479
25°	197	142
35°	12	10
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P170432

CATALOG NUMBER: LDA4A09840D010TE LAR25NF 4LA1

CANDELA DISTRIBUTION (FULL):

0°	
0°	4364.5
2.5°	4135.3
5°	3811.3
7.5°	3390.2
10°	2810.2
12.5°	2264.8
15°	1753.4
17.5°	1277.7
20°	904.6
22.5°	572.8
25°	196.9
27.5°	85.9
30°	45.2
32.5°	22.9
35°	12.3
37.5°	7.3
40°	3.9
42.5°	2.2
45°	1.1
47.5°	0.6
50°	0.6
52.5°	0.6
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.0
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)