

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210821

Luminaire Tested: **LE_4B10D010 EC4B10208030 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208030 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1275.6 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210821

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P210821

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102	109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88	102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77	95	87	81	77		84	79	75		82	78	74		79	76	73
4	90	81	73	68	88	79	73	68		77	71	67		75	70	66		73	69	65
5	84	73	66	61	82	72	65	60		70	64	60		69	63	59		67	62	59
6	79	67	60	54	77	66	59	54		65	58	54		63	58	53		62	57	53
7	74	62	54	49	72	61	54	49		60	53	49		58	53	48		57	52	48
8	69	57	50	45	68	57	50	45		55	49	45		54	49	44		53	48	44
9	65	53	46	41	64	53	46	41		52	45	41		51	45	41		50	44	41
10	61	50	43	38	60	49	42	38		48	42	38		47	42	38		46	41	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210821

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.6	6.5
10°-20°	210.6	16.5
20°-30°	273.0	21.4
30°-40°	267.4	21.0
40°-50°	226.7	17.8
50°-60°	148.6	11.6
60°-70°	59.7	4.7
70°-80°	6.8	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.2	44.4
0°-40°	833.6	65.4
0°-60°	1208.9	94.8
0°-90°	1275.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1275.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	911	
5°	887	83
15°	751	211
25°	596	273
35°	425	267
45°	295	227
55°	165	149
65°	58	60
75°	3	7
85°	0	0
90°	0	



TEST NUMBER: P210821

CATALOG NUMBER: LE_4B10D010 EC4B10208030 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	910.8
2.5°	903.9
5°	886.8
7.5°	858.6
10°	823.4
12.5°	785.2
15°	751.3
17.5°	714.6
20°	677.9
22.5°	638.3
25°	596.0
27.5°	552.2
30°	507.0
32.5°	464.6
35°	425.0
37.5°	392.5
40°	357.3
42.5°	326.2
45°	295.1
47.5°	262.6
50°	230.1
52.5°	197.7
55°	165.2
57.5°	135.6
60°	107.3
62.5°	81.9
65°	57.9
67.5°	38.2
70°	22.6
72.5°	9.9
75°	2.8
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)