

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210940

Luminaire Tested: **LE_4B10D010 EC4B10209035 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209035 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1075.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210940

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P210940

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	82	76	94	87	81	76	84	79	74		81	77	73		79
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72
5	83	73	65	59	82	72	64	59	70	63	59		68	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56
8	68	56	49	44	67	56	48	43	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	50	44	40		49	44	39		49
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210940

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.0	5.9
10°-20°	166.9	15.5
20°-30°	224.1	20.8
30°-40°	229.4	21.3
40°-50°	198.6	18.5
50°-60°	132.0	12.3
60°-70°	54.3	5.0
70°-80°	6.4	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	453.9	42.2
0°-40°	683.3	63.6
0°-60°	1014.0	94.3
0°-90°	1075.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	681	
5°	671	63
15°	596	167
25°	489	224
35°	366	229
45°	259	199
55°	146	132
65°	54	54
75°	3	6
85°	0	0
90°	0	



TEST NUMBER: P210940

CATALOG NUMBER: LE_4B10D010 EC4B10209035 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	681.3
2.5°	679.9
5°	670.7
7.5°	656.7
10°	637.7
12.5°	616.5
15°	596.0
17.5°	570.0
20°	544.6
22.5°	517.8
25°	488.9
27.5°	458.0
30°	427.0
32.5°	395.9
35°	366.3
37.5°	338.1
40°	311.5
42.5°	284.7
45°	258.6
47.5°	231.1
50°	202.9
52.5°	174.7
55°	146.5
57.5°	121.9
60°	96.5
62.5°	73.3
65°	53.6
67.5°	35.3
70°	20.4
72.5°	9.9
75°	2.8
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)