

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210965

Luminaire Tested: **LE_4B10D010 EC4B10208040 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208040 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1267.2 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210965

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P210965

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210965

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.1	4.9
10°-20°	168.7	13.3
20°-30°	234.3	18.5
30°-40°	255.7	20.2
40°-50°	238.5	18.8
50°-60°	181.1	14.3
60°-70°	99.1	7.8
70°-80°	27.3	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.1	36.7
0°-40°	720.8	56.9
0°-60°	1140.4	90.0
0°-90°	1267.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1267.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	663	
5°	657	62
15°	601	169
25°	509	234
35°	409	256
45°	310	239
55°	202	181
65°	99	99
75°	24	27
85°	0	0
90°	0	



TEST NUMBER: P210965

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	662.7
2.5°	662.7
5°	657.1
7.5°	648.8
10°	636.3
12.5°	619.4
15°	601.3
17.5°	579.1
20°	558.1
22.5°	533.0
25°	509.2
27.5°	485.6
30°	459.0
32.5°	434.0
35°	408.8
37.5°	383.7
40°	359.9
42.5°	334.9
45°	309.7
47.5°	284.7
50°	256.7
52.5°	230.3
55°	202.3
57.5°	175.9
60°	149.3
62.5°	122.7
65°	99.1
67.5°	76.8
70°	57.2
72.5°	39.1
75°	23.7
77.5°	11.1
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)