

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210971

Luminaire Tested: **LE_4B10D010 EC4B10208040 4LBW1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208040 4LBW1GPH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 844.5 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210971

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBW1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P210971

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBW1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210971

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBW1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	6.8
10°-20°	162.5	19.2
20°-30°	233.0	27.6
30°-40°	219.4	26.0
40°-50°	121.2	14.3
50°-60°	38.9	4.6
60°-70°	9.7	1.2
70°-80°	2.3	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.8	53.6
0°-40°	672.2	79.6
0°-60°	832.2	98.5
0°-90°	844.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	844.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	608	
5°	605	57
15°	576	162
25°	511	233
35°	356	219
45°	154	121
55°	40	39
65°	9	10
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P210971

CATALOG NUMBER: LE_4B10D010 EC4B10208040 4LBW1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	607.7
2.5°	603.4
5°	604.8
7.5°	600.4
10°	593.1
12.5°	585.8
15°	575.6
17.5°	566.8
20°	552.2
22.5°	531.6
25°	511.1
27.5°	483.3
30°	446.7
32.5°	405.7
35°	355.9
37.5°	303.1
40°	248.9
42.5°	199.2
45°	153.8
47.5°	115.7
50°	83.5
52.5°	58.6
55°	39.6
57.5°	26.3
60°	19.0
62.5°	13.2
65°	8.8
67.5°	5.9
70°	4.4
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)