

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211027

Luminaire Tested: **LE_4B10D010 EC4B10208050 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208050 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1284.8 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211027

CATALOG NUMBER: LE_4B10D010 EC4B10208050 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P211027

CATALOG NUMBER: LE_4B10D010 EC4B10208050 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	82	76	94	87	81	76	84	79	74		81	77	73		79
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72
5	83	73	65	59	82	72	64	59	70	63	59		68	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56
8	68	56	49	44	67	56	48	43	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	50	44	40		49	44	39		49
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211027

CATALOG NUMBER: LE_4B10D010 EC4B10208050 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.3	5.9
10°-20°	199.4	15.5
20°-30°	267.8	20.8
30°-40°	274.2	21.3
40°-50°	237.3	18.5
50°-60°	157.9	12.3
60°-70°	64.8	5.0
70°-80°	7.7	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.5	42.2
0°-40°	816.7	63.6
0°-60°	1211.9	94.3
0°-90°	1284.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	814	
5°	802	75
15°	712	199
25°	584	268
35°	438	274
45°	309	237
55°	175	158
65°	64	65
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P211027

CATALOG NUMBER: LE_4B10D010 EC4B10208050 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	814.3
2.5°	812.6
5°	801.7
7.5°	784.7
10°	762.0
12.5°	736.8
15°	712.4
17.5°	681.3
20°	650.9
22.5°	618.9
25°	584.4
27.5°	547.3
30°	510.3
32.5°	473.3
35°	437.9
37.5°	404.1
40°	372.2
42.5°	340.2
45°	309.0
47.5°	276.2
50°	242.6
52.5°	208.8
55°	175.2
57.5°	145.7
60°	115.3
62.5°	87.6
65°	64.0
67.5°	42.1
70°	24.5
72.5°	11.8
75°	3.4
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)