

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211125

Luminaire Tested: **LE_4B15D010 EC4B10209027 4LBM1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209027 4LBM1GPH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 769.2 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211125

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211125

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211125

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.8	9.5
10°-20°	189.8	24.7
20°-30°	243.4	31.6
30°-40°	175.9	22.9
40°-50°	63.1	8.2
50°-60°	17.0	2.2
60°-70°	5.6	0.7
70°-80°	1.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	506.0	65.8
0°-40°	681.9	88.6
0°-60°	762.0	99.1
0°-90°	769.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	791	
5°	776	73
15°	676	190
25°	537	243
35°	281	176
45°	76	63
55°	18	17
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P211125

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	790.9
2.5°	787.6
5°	776.3
7.5°	758.5
10°	734.3
12.5°	706.8
15°	676.0
17.5°	645.3
20°	614.6
22.5°	579.0
25°	537.0
27.5°	488.5
30°	427.0
32.5°	355.8
35°	281.4
37.5°	213.4
40°	155.2
42.5°	110.0
45°	76.0
47.5°	51.7
50°	34.0
52.5°	24.2
55°	17.7
57.5°	13.0
60°	9.7
62.5°	8.1
65°	4.9
67.5°	3.2
70°	3.2
72.5°	1.6
75°	1.6
77.5°	1.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)