

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211129

Luminaire Tested: **LE_4B15D010 EC4B10209027 4LBM1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211129
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209027 4LBM1WH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1094.1 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211129

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211129

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211129

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.1	11.0
10°-20°	308.6	28.2
20°-30°	362.1	33.1
30°-40°	229.1	20.9
40°-50°	61.3	5.6
50°-60°	8.6	0.8
60°-70°	3.2	0.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.8	72.3
0°-40°	1019.9	93.2
0°-60°	1089.9	99.6
0°-90°	1094.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1094.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1299	
5°	1278	120
15°	1106	309
25°	800	362
35°	364	229
45°	70	61
55°	8	9
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P211129

CATALOG NUMBER: LE_4B15D010 EC4B10209027 4LBM1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1299.4
2.5°	1294.6
5°	1278.4
7.5°	1252.6
10°	1215.4
12.5°	1167.0
15°	1105.5
17.5°	1042.5
20°	966.5
22.5°	888.9
25°	800.1
27.5°	703.1
30°	594.7
32.5°	476.8
35°	363.7
37.5°	263.4
40°	181.0
42.5°	116.3
45°	69.5
47.5°	38.7
50°	21.0
52.5°	11.4
55°	8.1
57.5°	6.5
60°	4.9
62.5°	4.9
65°	3.2
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)