

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211163

Luminaire Tested: **LE_4B15D010 EC4B10209727 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211163
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209727 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 883.6 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211163

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211163

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48			
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211163

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	7.8
10°-20°	181.4	20.5
20°-30°	238.8	27.0
30°-40°	185.9	21.0
40°-50°	90.3	10.2
50°-60°	57.0	6.5
60°-70°	36.8	4.2
70°-80°	19.2	2.2
80°-90°	4.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.6	55.4
0°-40°	675.4	76.4
0°-60°	822.8	93.1
0°-90°	883.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	883.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	754	
5°	740	69
15°	647	181
25°	526	239
35°	298	186
45°	112	90
55°	63	57
65°	36	37
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P211163

CATALOG NUMBER: LE_4B15D010 EC4B10209727 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	753.8
2.5°	749.6
5°	739.7
7.5°	722.9
10°	700.4
12.5°	675.1
15°	647.0
17.5°	617.6
20°	586.7
22.5°	557.3
25°	526.4
27.5°	487.1
30°	433.7
32.5°	370.6
35°	297.5
37.5°	230.1
40°	178.3
42.5°	139.0
45°	112.3
47.5°	91.3
50°	80.0
52.5°	71.6
55°	63.2
57.5°	56.1
60°	49.2
62.5°	42.1
65°	36.5
67.5°	32.2
70°	26.7
72.5°	22.5
75°	18.2
77.5°	14.0
80°	9.9
82.5°	7.1
85°	4.2
87.5°	1.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)