

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211197

Luminaire Tested: **LE_4B15D010 EC4B10208030 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208030 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1703.2 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211197

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBS1H

Luminous Intensity Polar Plot






TEST NUMBER: P211197

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211197

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	4.9
10°-20°	226.8	13.3
20°-30°	315.0	18.5
30°-40°	343.7	20.2
40°-50°	320.6	18.8
50°-60°	243.3	14.3
60°-70°	133.3	7.8
70°-80°	36.7	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.2	36.7
0°-40°	968.9	56.9
0°-60°	1532.8	90.0
0°-90°	1703.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	891	
5°	883	83
15°	808	227
25°	684	315
35°	550	344
45°	416	321
55°	272	243
65°	133	133
75°	32	37
85°	0	1
90°	0	



TEST NUMBER: P211197

CATALOG NUMBER: LE_4B15D010 EC4B10208030 4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	890.8
2.5°	890.8
5°	883.2
7.5°	872.0
10°	855.2
12.5°	832.6
15°	808.3
17.5°	778.2
20°	750.2
22.5°	716.4
25°	684.5
27.5°	652.6
30°	617.0
32.5°	583.2
35°	549.5
37.5°	515.7
40°	483.8
42.5°	450.1
45°	416.3
47.5°	382.6
50°	345.1
52.5°	309.4
55°	271.9
57.5°	236.3
60°	200.7
62.5°	165.1
65°	133.2
67.5°	103.1
70°	76.9
72.5°	52.5
75°	31.9
77.5°	15.0
80°	3.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)