

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777338

Luminaire Tested: LERS4D05D010-EC4DR200210IC9050-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P777338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D05D010-EC4DR200210IC9050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 797.8 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 7.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777338

CATALOG NUMBER: LERS4D05D010-EC4DR200210IC9050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P777338

CATALOG NUMBER: LERS4D05D010-EC4DR200210IC9050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100	100														
	1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97	97	97	97	97	97	97	97	97	97														
	2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94	94	94	94	94	94	94	94	94	94														
	3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91	91	91	91	91	91	91	91	91	91														
	4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88	88	88	88	88	88	88	88	88	88														
	5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85	85	85	85	85	85	85	85	85	85														
	6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83	83	83	83	83	83	83	83	83	83														
	7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81	81	81	81	81	81	81	81	81	81														
	8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79	79	79	79	79	79	79	79	79	79														
	9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77	77	77	77	77	77	77	77	77	77														
	10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75	75	75	75	75	75	75	75	75	75														

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	496164
5°	447629
10°	251238
15°	127707
20°	54067
25°	24955
30°	13209
35°	7123
40°	3808
45°	2256
50°	1309
55°	686
60°	437
65°	310
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2256 cd/sqm



TEST NUMBER: P777338

CATALOG NUMBER: LERS4D05D010-EC4DR200210IC9050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	323.3	40.5
10°-20°	318.4	39.9
20°-30°	104.0	13.0
30°-40°	35.4	4.4
40°-50°	11.9	1.5
50°-60°	3.6	0.4
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	745.7	93.5
0°-40°	781.1	97.9
0°-60°	796.6	99.8
0°-90°	797.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4541	
5°	4081	323
15°	1129	318
25°	207	104
35°	53	35
45°	15	12
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P777338

CATALOG NUMBER: LERS4D05D010-EC4DR200210IC9050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4541.1
0.5°	4541.1
1°	4535.4
1.5°	4524.1
2°	4503.5
2.5°	4476.0
3°	4437.1
3.5°	4383.0
4°	4302.5
4.5°	4204.6
5°	4081.3
5.5°	3919.1
6°	3753.0
6.5°	3562.5
7°	3376.1
7.5°	3157.7
8°	2962.8
8.5°	2766.7
9°	2585.5
9.5°	2419.3
10°	2264.5
12.5°	1626.0
15°	1129.0
17.5°	737.6
20°	465.0
22.5°	301.3
25°	207.0
27.5°	145.6
30°	104.7
32.5°	75.2
35°	53.4
37.5°	37.2
40°	26.7
42.5°	19.4
45°	14.6
47.5°	11.3
50°	7.7
52.5°	4.9
55°	3.6
57.5°	2.8
60°	2.0
62.5°	1.6
65°	1.2



TEST NUMBER: P777338

CATALOG NUMBER: LERS4D05D010-EC4DR200210IC9050-4LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)