

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211233

Luminaire Tested: **LE_4B15D010 EC4B10209030 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209030 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1238.6 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211233

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4L1BWH

Luminous Intensity Polar Plot





TEST NUMBER: P211233

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211233

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4L1BWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.0	6.1
10°-20°	219.1	17.7
20°-30°	323.3	26.1
30°-40°	319.0	25.8
40°-50°	195.2	15.8
50°-60°	74.9	6.0
60°-70°	23.4	1.9
70°-80°	6.9	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.4	49.9
0°-40°	937.3	75.7
0°-60°	1207.4	97.5
0°-90°	1238.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1238.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	798	
5°	798	76
15°	776	219
25°	708	323
35°	518	319
45°	250	195
55°	79	75
65°	22	23
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P211233

CATALOG NUMBER: LE_4B15D010 EC4B10209030 4L1BWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	798.3
2.5°	799.9
5°	798.3
7.5°	796.6
10°	791.6
12.5°	784.9
15°	776.5
17.5°	766.4
20°	751.2
22.5°	734.4
25°	707.6
27.5°	674.0
30°	632.0
32.5°	579.8
35°	517.6
37.5°	448.7
40°	378.2
42.5°	312.6
45°	250.4
47.5°	195.0
50°	147.9
52.5°	109.3
55°	79.0
57.5°	55.4
60°	40.4
62.5°	30.3
65°	21.8
67.5°	16.8
70°	11.7
72.5°	8.4
75°	6.7
77.5°	3.4
80°	3.4
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)