

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211276

Luminaire Tested: **LE_4B15D010 EC4B10208035 4LBN1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208035 4LBN1B
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 689.7 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211276

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1B

Luminous Intensity Polar Plot






TEST NUMBER: P211276

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107	111	109	107	105		105	103	102			101	100	99			98
2	109	104	100	97	106	102	99	96		99	96	94			96	94	92			93
3	104	98	93	89	102	96	92	88		94	90	87			91	88	86			89
4	99	92	86	82	97	90	86	82		88	84	81			86	83	80			85
5	94	86	81	77	92	85	80	76		84	79	76			82	78	75			80
6	90	81	76	72	88	81	75	71		79	74	71			78	74	70			76
7	86	77	71	67	84	76	71	67		75	70	67			74	69	66			73
8	82	73	67	63	80	72	67	63		71	66	63			70	66	62			69
9	78	69	63	60	77	68	63	59		67	63	59			67	62	59			66
10	75	65	60	56	74	65	60	56		64	59	56			63	59	56			63

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211276

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.0	13.6
10°-20°	199.3	28.9
20°-30°	231.2	33.5
30°-40°	144.8	21.0
40°-50°	20.4	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.5	76.0
0°-40°	669.2	97.0
0°-60°	689.7	100.0
0°-90°	689.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1128	
5°	1045	94
15°	708	199
25°	510	231
35°	232	145
45°	18	20
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211276

CATALOG NUMBER: LE_4B15D010 EC4B10208035 4LBN1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1127.6
2.5°	1105.5
5°	1044.9
7.5°	958.2
10°	869.4
12.5°	784.7
15°	708.1
17.5°	643.5
20°	595.1
22.5°	550.7
25°	510.4
27.5°	461.9
30°	399.4
32.5°	320.7
35°	232.0
37.5°	151.3
40°	86.8
42.5°	44.4
45°	18.2
47.5°	4.1
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)