

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211349

Luminaire Tested: **LE_4B15D010 EC4B10208040 4L1BWH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208040 4L1BWH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1502.0 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211349

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4L1BWH

Luminous Intensity Polar Plot





TEST NUMBER: P211349

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4L1BWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211349

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4L1BWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	6.1
10°-20°	265.6	17.7
20°-30°	392.0	26.1
30°-40°	386.8	25.8
40°-50°	236.7	15.8
50°-60°	90.8	6.0
60°-70°	28.4	1.9
70°-80°	8.3	0.6
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.8	49.9
0°-40°	1136.7	75.7
0°-60°	1464.2	97.5
0°-90°	1502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	968	
5°	968	92
15°	942	266
25°	858	392
35°	628	387
45°	304	237
55°	96	91
65°	26	28
75°	8	8
85°	0	1
90°	0	



TEST NUMBER: P211349

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4L1BWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	968.0
2.5°	970.1
5°	968.0
7.5°	966.0
10°	959.9
12.5°	951.8
15°	941.6
17.5°	929.4
20°	910.9
22.5°	890.6
25°	858.1
27.5°	817.2
30°	766.3
32.5°	703.1
35°	627.7
37.5°	544.2
40°	458.5
42.5°	379.1
45°	303.7
47.5°	236.4
50°	179.3
52.5°	132.5
55°	95.8
57.5°	67.3
60°	49.0
62.5°	36.7
65°	26.4
67.5°	20.4
70°	14.3
72.5°	10.2
75°	8.1
77.5°	4.1
80°	4.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)