

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211343

Luminaire Tested: **LE_4B15D010 EC4B10208040 4LBS1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208040 4LBS1LI
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1840.3 lumens
Efficiency: N/A
Efficacy: 128.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211343

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211343

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71		
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57		
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51		
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211343

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.1	6.5
10°-20°	303.9	16.5
20°-30°	393.8	21.4
30°-40°	385.8	21.0
40°-50°	327.0	17.8
50°-60°	214.4	11.7
60°-70°	86.2	4.7
70°-80°	9.9	0.5
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	816.8	44.4
0°-40°	1202.6	65.3
0°-60°	1744.0	94.8
0°-90°	1840.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1840.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1314	
5°	1279	119
15°	1084	304
25°	860	394
35°	613	386
45°	426	327
55°	238	214
65°	84	86
75°	4	10
85°	0	0
90°	0	



TEST NUMBER: P211343

CATALOG NUMBER: LE_4B15D010 EC4B10208040 4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1313.9
2.5°	1303.7
5°	1279.4
7.5°	1238.5
10°	1187.6
12.5°	1132.6
15°	1083.8
17.5°	1030.8
20°	977.9
22.5°	920.8
25°	859.7
27.5°	796.6
30°	731.4
32.5°	670.2
35°	613.2
37.5°	566.3
40°	515.4
42.5°	470.6
45°	425.7
47.5°	378.9
50°	332.1
52.5°	285.2
55°	238.4
57.5°	195.6
60°	154.9
62.5°	118.2
65°	83.5
67.5°	55.0
70°	32.6
72.5°	14.3
75°	4.1
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)