

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211366

Luminaire Tested: **LE_4B15D010 EC4B10209040 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10209040 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1073.9 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211366

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211366

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211366

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	7.8
10°-20°	220.5	20.5
20°-30°	290.2	27.0
30°-40°	225.9	21.0
40°-50°	109.7	10.2
50°-60°	69.3	6.5
60°-70°	44.7	4.2
70°-80°	23.4	2.2
80°-90°	5.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.0	55.4
0°-40°	821.0	76.4
0°-60°	1000.0	93.1
0°-90°	1073.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1073.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	916	
5°	899	84
15°	786	221
25°	640	290
35°	362	226
45°	136	110
55°	77	69
65°	44	45
75°	22	23
85°	5	6
90°	0	



TEST NUMBER: P211366

CATALOG NUMBER: LE_4B15D010 EC4B10209040 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	916.2
2.5°	911.1
5°	899.1
7.5°	878.6
10°	851.3
12.5°	820.6
15°	786.5
17.5°	750.6
20°	713.2
22.5°	677.3
25°	639.7
27.5°	591.9
30°	527.2
32.5°	450.4
35°	361.7
37.5°	279.8
40°	216.7
42.5°	168.9
45°	136.5
47.5°	110.9
50°	97.2
52.5°	87.0
55°	76.8
57.5°	68.2
60°	59.7
62.5°	51.2
65°	44.3
67.5°	39.2
70°	32.4
72.5°	27.3
75°	22.2
77.5°	17.1
80°	11.9
82.5°	8.6
85°	5.1
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)