

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211404

Luminaire Tested: **LE_4B15D010 EC4B10208050 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B15D010 EC4B10208050 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1788.1 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211404

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P211404

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	82	76	94	87	81	76	84	79	74		81	77	73		79
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72
5	83	73	65	59	82	72	64	59	70	63	59		68	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56
8	68	56	49	44	67	56	48	43	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	50	44	40		49	44	39		49
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211404

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	5.9
10°-20°	277.6	15.5
20°-30°	372.8	20.8
30°-40°	381.6	21.3
40°-50°	330.3	18.5
50°-60°	219.7	12.3
60°-70°	90.2	5.0
70°-80°	10.7	0.6
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.1	42.2
0°-40°	1136.7	63.6
0°-60°	1686.7	94.3
0°-90°	1788.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1788.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1133	
5°	1116	105
15°	992	278
25°	813	373
35°	610	382
45°	430	330
55°	244	220
65°	89	90
75°	5	11
85°	0	0
90°	0	



TEST NUMBER: P211404

CATALOG NUMBER: LE_4B15D010 EC4B10208050 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1133.3
2.5°	1130.9
5°	1115.7
7.5°	1092.3
10°	1060.6
12.5°	1025.4
15°	991.5
17.5°	948.1
20°	906.0
22.5°	861.4
25°	813.3
27.5°	761.8
30°	710.2
32.5°	658.6
35°	609.5
37.5°	562.5
40°	517.9
42.5°	473.5
45°	430.1
47.5°	384.4
50°	337.6
52.5°	290.7
55°	243.7
57.5°	202.8
60°	160.5
62.5°	121.9
65°	89.1
67.5°	58.6
70°	34.0
72.5°	16.4
75°	4.6
77.5°	2.3
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)