

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211475

Luminaire Tested: **LE_4B20D010 EC4B10208027 4LBM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208027 4LBM1LI
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2108.4 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211475

CATALOG NUMBER: LE_4B20D010 EC4B10208027 4LBM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211475

CATALOG NUMBER: LE_4B20D010 EC4B10208027 4LBM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211475

CATALOG NUMBER: LE_4B20D010 EC4B10208027 4LBM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.9	14.3
10°-20°	672.8	31.9
20°-30°	668.9	31.7
30°-40°	364.3	17.3
40°-50°	84.2	4.0
50°-60°	11.9	0.6
60°-70°	4.4	0.2
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1642.6	77.9
0°-40°	2006.9	95.2
0°-60°	2103.0	99.7
0°-90°	2108.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2108.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3324	
5°	3255	301
15°	2428	673
25°	1467	669
35°	564	364
45°	97	84
55°	13	12
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P211475

CATALOG NUMBER: LE_4B20D010 EC4B10208027 4LBM1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3323.6
2.5°	3316.0
5°	3254.7
7.5°	3129.8
10°	2956.4
12.5°	2701.3
15°	2428.3
17.5°	2157.9
20°	1892.7
22.5°	1675.9
25°	1466.7
27.5°	1267.8
30°	1043.3
32.5°	793.3
35°	563.8
37.5°	380.0
40°	247.4
42.5°	155.6
45°	97.0
47.5°	56.1
50°	28.1
52.5°	15.3
55°	12.8
57.5°	7.7
60°	7.7
62.5°	5.1
65°	5.1
67.5°	2.6
70°	2.6
72.5°	2.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)