

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777608

Luminaire Tested: LERS4D08D010-EC4DR150210IC9027-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P777608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D08D010-EC4DR150210IC9027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 722.3 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777608

CATALOG NUMBER: LERS4D08D010-EC4DR150210IC9027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P777608

CATALOG NUMBER: LERS4D08D010-EC4DR150210IC9027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1107410	1107410	1107410
5°	650771	642345	647427
10°	194220	195582	198577
15°	48310	49248	47737
20°	14458	16741	14761
25°	5095	6489	5157
30°	1872	2464	1902
35°	937	1060	908
40°	589	653	589
45°	434	469	434
50°	348	348	348
55°	292	292	292
60°	232	232	232
65°	178	178	178
70°	154	154	154
75°	91	91	128
80°	63	63	63
85°	33	33	33

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 469 cd/sqm



TEST NUMBER: P777608

CATALOG NUMBER: LERS4D08D010-EC4DR150210IC9027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.5	64.9
10°-20°	192.7	26.7
20°-30°	38.3	5.3
30°-40°	9.5	1.3
40°-50°	5.0	0.7
50°-60°	3.7	0.5
60°-70°	2.6	0.4
70°-80°	1.5	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.5	96.8
0°-40°	709.0	98.2
0°-60°	717.7	99.4
0°-90°	722.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	722.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	9842	9842	9842	9842	9842	
5°	6403	6338	6320	6364	6370	468
15°	556	567	567	557	550	191
25°	65	74	83	74	66	34
35°	13	14	15	14	12	9
45°	6	6	7	6	6	5
55°	4	4	4	4	4	4
65°	2	2	2	2	2	3
75°	1	1	1	1	2	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P777608

CATALOG NUMBER: LERS4D08D010-EC4DR150210IC9027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	9841.9	9841.9	9841.9	9841.9	9841.9
2.5°	8877.8	8885.3	8888.2	8897.0	8929.5
5°	6403.4	6337.5	6320.5	6364.2	6370.5
7.5°	3793.1	3806.4	3855.2	3866.0	3826.9
10°	2081.5	2098.6	2096.1	2111.1	2128.2
12.5°	1064.5	1051.2	1047.0	1064.1	1040.4
15°	556.2	566.6	567.0	557.0	549.6
17.5°	299.1	311.2	331.2	315.0	290.0
20°	176.7	187.5	204.6	191.2	180.4
22.5°	109.2	117.9	130.0	119.6	110.8
25°	65.4	74.2	83.3	73.7	66.2
27.5°	38.7	46.2	52.1	45.8	38.3
30°	25.0	29.2	32.9	28.7	25.4
32.5°	17.5	19.2	20.8	19.2	17.5
35°	12.9	13.7	14.6	13.7	12.5
37.5°	10.0	10.8	11.2	10.4	9.6
40°	8.3	8.7	9.2	8.7	8.3
42.5°	7.1	7.5	7.5	7.5	7.1
45°	6.2	6.2	6.7	6.2	6.2
47.5°	5.4	5.4	5.8	5.4	5.4
50°	5.0	5.0	5.0	5.0	5.0
52.5°	4.6	4.6	4.6	4.6	4.6
55°	4.2	4.2	4.2	4.2	4.2
57.5°	3.7	3.7	3.7	3.7	3.7
60°	3.3	3.3	3.3	3.3	3.3
62.5°	2.9	2.9	2.9	2.9	2.9
65°	2.5	2.5	2.5	2.5	2.5
67.5°	2.5	2.5	2.5	2.5	2.5
70°	2.1	2.1	2.1	2.1	2.1
72.5°	1.7	1.7	1.7	1.7	1.7
75°	1.2	1.2	1.2	1.2	1.7
77.5°	1.2	1.2	1.2	1.2	1.2
80°	0.8	0.8	0.8	0.8	0.8
82.5°	0.8	0.8	0.8	0.8	0.8
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)