

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211503

Luminaire Tested: **LE\_4B20D010 EC4B10209027 4LBM1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211503  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10209027 4LBM1H  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1450.6 lumens  
Efficiency: N/A  
Efficacy: 69.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211503  
CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBM1H

### Luminous Intensity Polar Plot





TEST NUMBER: P211503

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBM1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211503

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBM1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.4	9.1
10°-20°	347.2	23.9
20°-30°	446.3	30.8
30°-40°	335.8	23.1
40°-50°	134.8	9.3
50°-60°	38.3	2.6
60°-70°	12.1	0.8
70°-80°	3.5	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	925.9	63.8
0°-40°	1261.6	87.0
0°-60°	1434.7	98.9
0°-90°	1450.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1450.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1438	
5°	1412	132
15°	1239	347
25°	985	446
35°	539	336
45°	166	135
55°	39	38
65°	11	12
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211503

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBM1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1438.4
2.5°	1429.7
5°	1412.2
7.5°	1379.2
10°	1337.7
12.5°	1287.4
15°	1239.2
17.5°	1184.5
20°	1125.3
22.5°	1061.9
25°	985.2
27.5°	893.3
30°	786.0
32.5°	665.6
35°	538.6
37.5°	420.4
40°	315.3
42.5°	232.1
45°	166.3
47.5°	113.8
50°	78.8
52.5°	54.8
55°	39.4
57.5°	28.4
60°	21.9
62.5°	15.3
65°	10.9
67.5°	8.7
70°	6.6
72.5°	4.4
75°	2.2
77.5°	2.2
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)