

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211516

Luminaire Tested: **LE_4B20D010 EC4B10209027 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211516
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209027 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1894.5 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211516
CATALOG NUMBER: LE_4B20D010 EC4B10209027 4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P211516

CATALOG NUMBER: LE_4B20D010 EC4B10209027 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211516

CATALOG NUMBER: LE_4B20D010 EC4B10209027 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.8	4.9
10°-20°	252.2	13.3
20°-30°	350.3	18.5
30°-40°	382.3	20.2
40°-50°	356.6	18.8
50°-60°	270.7	14.3
60°-70°	148.2	7.8
70°-80°	40.8	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.4	36.7
0°-40°	1077.6	56.9
0°-60°	1704.9	90.0
0°-90°	1894.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1894.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	991	
5°	982	93
15°	899	252
25°	761	350
35°	611	382
45°	463	357
55°	302	271
65°	148	148
75°	36	41
85°	0	1
90°	0	



TEST NUMBER: P211516

CATALOG NUMBER: LE_4B20D010 EC4B10209027 4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	990.9
2.5°	990.9
5°	982.5
7.5°	970.0
10°	951.2
12.5°	926.1
15°	899.0
17.5°	865.7
20°	834.4
22.5°	796.8
25°	761.3
27.5°	725.9
30°	686.3
32.5°	648.7
35°	611.2
37.5°	573.6
40°	538.1
42.5°	500.7
45°	463.1
47.5°	425.5
50°	383.8
52.5°	344.2
55°	302.4
57.5°	262.9
60°	223.2
62.5°	183.5
65°	148.1
67.5°	114.7
70°	85.5
72.5°	58.3
75°	35.5
77.5°	16.7
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)