

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777637

Luminaire Tested: LERS4D08D010-EC4DR200210IC9030-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P777637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D08D010-EC4DR200210IC9030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 833.8 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P777637

CATALOG NUMBER: LERS4D08D010-EC4DR200210IC9030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P777637

CATALOG NUMBER: LERS4D08D010-EC4DR200210IC9030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	518552
5°	467832
10°	262577
15°	133464
20°	56509
25°	26088
30°	13815
35°	7443
40°	3979
45°	2349
50°	1360
55°	724
60°	459
65°	336
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2349 cd/sqm



TEST NUMBER: P777637

CATALOG NUMBER: LERS4D08D010-EC4DR200210IC9030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.9	40.5
10°-20°	332.7	39.9
20°-30°	108.7	13.0
30°-40°	37.0	4.4
40°-50°	12.4	1.5
50°-60°	3.8	0.5
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.3	93.5
0°-40°	816.3	97.9
0°-60°	832.5	99.8
0°-90°	833.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4746	
5°	4266	338
15°	1180	333
25°	216	109
35°	56	37
45°	15	12
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P777637

CATALOG NUMBER: LERS4D08D010-EC4DR200210IC9030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4746.0
0.5°	4746.0
1°	4740.1
1.5°	4728.2
2°	4706.7
2.5°	4677.9
3°	4637.4
3.5°	4580.7
4°	4496.6
4.5°	4394.4
5°	4265.5
5.5°	4096.0
6°	3922.3
6.5°	3723.2
7°	3528.4
7.5°	3300.2
8°	3096.5
8.5°	2891.5
9°	2702.2
9.5°	2528.5
10°	2366.7
12.5°	1699.3
15°	1179.9
17.5°	770.9
20°	486.0
22.5°	314.8
25°	216.4
27.5°	152.1
30°	109.5
32.5°	78.6
35°	55.8
37.5°	38.9
40°	27.9
42.5°	20.3
45°	15.2
47.5°	11.8
50°	8.0
52.5°	5.1
55°	3.8
57.5°	3.0
60°	2.1
62.5°	1.7
65°	1.3



TEST NUMBER: P777637

CATALOG NUMBER: LERS4D08D010-EC4DR200210IC9030-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.8
70°		0.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)