

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211522

Luminaire Tested: **LE\_4B20D010 EC4B10209027 4LBW1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211522  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10209027 4LBW1GPH  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1262.5 lumens  
Efficiency: N/A  
Efficacy: 60.7 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211522

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBW1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P211522

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBW1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							100												
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92							92												
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83							83												
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76							76												
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69							69												
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63							63												
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57							57												
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53							53												
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48							48												
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45							45												
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41							41												

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211522

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBW1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.7	6.8
10°-20°	242.9	19.2
20°-30°	348.3	27.6
30°-40°	328.0	26.0
40°-50°	181.1	14.3
50°-60°	58.1	4.6
60°-70°	14.5	1.2
70°-80°	3.5	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.0	53.6
0°-40°	1004.9	79.6
0°-60°	1244.2	98.6
0°-90°	1262.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1262.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	909	
5°	904	86
15°	860	243
25°	764	348
35°	532	328
45°	230	181
55°	59	58
65°	13	15
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P211522

CATALOG NUMBER: LE\_4B20D010 EC4B10209027 4LBW1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	908.6
2.5°	902.1
5°	904.2
7.5°	897.7
10°	886.7
12.5°	875.8
15°	860.5
17.5°	847.4
20°	825.5
22.5°	794.8
25°	764.1
27.5°	722.6
30°	667.8
32.5°	606.4
35°	532.1
37.5°	453.2
40°	372.2
42.5°	297.8
45°	229.9
47.5°	173.0
50°	124.8
52.5°	87.6
55°	59.2
57.5°	39.4
60°	28.4
62.5°	19.7
65°	13.1
67.5°	8.8
70°	6.6
72.5°	4.4
75°	2.2
77.5°	2.2
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)