

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211534

Luminaire Tested: **LE_4B20D010 EC4B10209727 4LBM1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209727 4LBM1MW
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1313.1 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211534

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4LBM1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211534

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4LBM1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211534

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4LBM1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.4	7.0
10°-20°	247.7	18.9
20°-30°	329.4	25.1
30°-40°	269.4	20.5
40°-50°	156.9	11.9
50°-60°	104.1	7.9
60°-70°	68.4	5.2
70°-80°	36.1	2.8
80°-90°	8.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	669.5	51.0
0°-40°	938.8	71.5
0°-60°	1199.8	91.4
0°-90°	1313.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1313.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	997	
5°	985	92
15°	883	248
25°	723	329
35°	430	269
45°	198	157
55°	116	104
65°	68	68
75°	34	36
85°	8	9
90°	0	



TEST NUMBER: P211534

CATALOG NUMBER: LE_4B20D010 EC4B10209727 4LBM1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	996.8
2.5°	994.9
5°	985.4
7.5°	962.6
10°	937.9
12.5°	915.0
15°	882.6
17.5°	846.6
20°	816.1
22.5°	774.3
25°	722.9
27.5°	667.7
30°	597.3
32.5°	513.6
35°	429.9
37.5°	353.8
40°	287.2
42.5°	235.9
45°	197.9
47.5°	167.4
50°	146.5
52.5°	129.3
55°	116.0
57.5°	102.8
60°	89.4
62.5°	79.9
65°	68.4
67.5°	58.9
70°	49.4
72.5°	41.9
75°	34.2
77.5°	26.7
80°	19.0
82.5°	13.3
85°	7.7
87.5°	1.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)