

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211573

Luminaire Tested: **LE_4B20D010 EC4B10208030 4LBS1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208030 4LBS1GPH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2116.8 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211573

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBS1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211573

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBS1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211573

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBS1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	4.4
10°-20°	259.8	12.3
20°-30°	379.0	17.9
30°-40°	432.2	20.4
40°-50°	414.5	19.6
50°-60°	317.5	15.0
60°-70°	174.2	8.2
70°-80°	46.3	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	731.3	34.6
0°-40°	1163.5	55.0
0°-60°	1895.5	89.5
0°-90°	2116.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2116.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	983	
5°	976	93
15°	922	260
25°	823	379
35°	691	432
45°	539	415
55°	356	318
65°	175	174
75°	41	46
85°	0	1
90°	0	



TEST NUMBER: P211573

CATALOG NUMBER: LE_4B20D010 EC4B10208030 4LBS1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	983.1
2.5°	980.5
5°	975.6
7.5°	967.9
10°	957.7
12.5°	939.9
15°	922.2
17.5°	901.8
20°	878.9
22.5°	851.0
25°	823.1
27.5°	795.2
30°	759.6
32.5°	726.5
35°	691.0
37.5°	655.4
40°	619.9
42.5°	581.7
45°	538.6
47.5°	495.3
50°	449.6
52.5°	401.4
55°	355.7
57.5°	310.0
60°	261.7
62.5°	215.9
65°	175.3
67.5°	134.7
70°	99.1
72.5°	66.0
75°	40.6
77.5°	17.7
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)