

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211634

Luminaire Tested: **LE_4B20D010 EC4B10209730 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209730 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1796.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211634

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211634

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211634

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	3.8
10°-20°	195.4	10.9
20°-30°	294.3	16.4
30°-40°	350.2	19.5
40°-50°	349.6	19.5
50°-60°	284.3	15.8
60°-70°	174.9	9.7
70°-80°	67.8	3.8
80°-90°	10.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.3	31.1
0°-40°	908.6	50.6
0°-60°	1542.5	85.9
0°-90°	1796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	724	
5°	722	69
15°	694	195
25°	641	294
35°	561	350
45°	454	350
55°	318	284
65°	176	175
75°	62	68
85°	8	11
90°	0	



TEST NUMBER: P211634

CATALOG NUMBER: LE_4B20D010 EC4B10209730 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	723.6
2.5°	724.7
5°	721.5
7.5°	717.2
10°	711.9
12.5°	702.4
15°	693.8
17.5°	681.0
20°	667.2
22.5°	654.5
25°	640.7
27.5°	621.4
30°	602.3
32.5°	584.2
35°	560.9
37.5°	535.2
40°	511.9
42.5°	483.1
45°	454.4
47.5°	423.5
50°	390.6
52.5°	356.5
55°	318.2
57.5°	281.0
60°	244.8
62.5°	209.6
65°	175.6
67.5°	143.6
70°	113.9
72.5°	86.2
75°	61.7
77.5°	40.5
80°	24.5
82.5°	14.8
85°	8.5
87.5°	4.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)