

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P777949

Luminaire Tested: LERS4D10D010-EC4DR200210IC9030-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P777949  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS4D10D010-EC4DR200210IC9030-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1114.7 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P777949

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9030-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P777949

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9030-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	693238
5°	625428
10°	351023
15°	178428
20°	75542
25°	34877
30°	18458
35°	9950
40°	5320
45°	3137
50°	1819
55°	972
60°	612
65°	440
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3137 cd/sqm



TEST NUMBER: P777949

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9030-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	451.7	40.5
10°-20°	444.8	39.9
20°-30°	145.3	13.0
30°-40°	49.5	4.4
40°-50°	16.6	1.5
50°-60°	5.0	0.5
60°-70°	1.7	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1041.9	93.5
0°-40°	1091.3	97.9
0°-60°	1113.0	99.8
0°-90°	1114.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1114.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6345	
5°	5702	452
15°	1577	445
25°	289	145
35°	75	49
45°	20	17
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P777949

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9030-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6344.8
0.5°	6344.8
1°	6336.9
1.5°	6321.1
2°	6292.3
2.5°	6253.8
3°	6199.6
3.5°	6123.9
4°	6011.5
4.5°	5874.7
5°	5702.4
5.5°	5475.9
6°	5243.6
6.5°	4977.5
7°	4717.1
7.5°	4412.0
8°	4139.7
8.5°	3865.6
9°	3612.5
9.5°	3380.3
10°	3163.9
12.5°	2271.8
15°	1577.4
17.5°	1030.5
20°	649.7
22.5°	420.9
25°	289.3
27.5°	203.4
30°	146.3
32.5°	105.1
35°	74.6
37.5°	52.0
40°	37.3
42.5°	27.1
45°	20.3
47.5°	15.8
50°	10.7
52.5°	6.8
55°	5.1
57.5°	4.0
60°	2.8
62.5°	2.3
65°	1.7



TEST NUMBER: P777949

CATALOG NUMBER: LERS4D10D010-EC4DR200210IC9030-4LBS1H

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.1
70°		0.6

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)