

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211725

Luminaire Tested: **LE\_4B20D010 EC4B10208040 4LBW1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10208040 4LBW1GPH  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1592.4 lumens  
Efficiency: N/A  
Efficacy: 76.6 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211725

CATALOG NUMBER: LE\_4B20D010 EC4B10208040 4LBW1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P211725

CATALOG NUMBER: LE\_4B20D010 EC4B10208040 4LBW1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211725

CATALOG NUMBER: LE\_4B20D010 EC4B10208040 4LBW1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	6.8
10°-20°	306.4	19.2
20°-30°	439.4	27.6
30°-40°	413.7	26.0
40°-50°	228.5	14.3
50°-60°	73.3	4.6
60°-70°	18.3	1.1
70°-80°	4.4	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	853.9	53.6
0°-40°	1267.6	79.6
0°-60°	1569.4	98.6
0°-90°	1592.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1592.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1146	
5°	1141	108
15°	1085	306
25°	964	439
35°	671	414
45°	290	228
55°	75	73
65°	17	18
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P211725

CATALOG NUMBER: LE\_4B20D010 EC4B10208040 4LBW1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1146.1
2.5°	1137.8
5°	1140.6
7.5°	1132.3
10°	1118.5
12.5°	1104.7
15°	1085.4
17.5°	1068.8
20°	1041.2
22.5°	1002.5
25°	963.8
27.5°	911.4
30°	842.4
32.5°	765.0
35°	671.1
37.5°	571.6
40°	469.5
42.5°	375.6
45°	290.0
47.5°	218.2
50°	157.4
52.5°	110.4
55°	74.6
57.5°	49.8
60°	36.0
62.5°	24.8
65°	16.6
67.5°	11.0
70°	8.2
72.5°	5.6
75°	2.8
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)