

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211737

Luminaire Tested: **LE\_4B20D010 EC4B10209040 4LBM1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211737  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10209040 4LBM1MW  
Description: PORTFOLIO 4 INCH CYLINDER  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1595.0 lumens  
Efficiency: N/A  
Efficacy: 76.7 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211737

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBM1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P211737

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBM1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211737

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBM1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	112.2	7.0
10°-20°	300.9	18.9
20°-30°	400.0	25.1
30°-40°	327.2	20.5
40°-50°	190.6	11.9
50°-60°	126.4	7.9
60°-70°	83.2	5.2
70°-80°	43.9	2.8
80°-90°	10.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	813.1	51.0
0°-40°	1140.3	71.5
0°-60°	1457.3	91.4
0°-90°	1595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1595.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1211	
5°	1197	112
15°	1072	301
25°	878	400
35°	522	327
45°	240	191
55°	141	126
65°	83	83
75°	42	44
85°	9	11
90°	0	



TEST NUMBER: P211737

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBM1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1210.8
2.5°	1208.5
5°	1196.9
7.5°	1169.2
10°	1139.1
12.5°	1111.4
15°	1072.2
17.5°	1028.2
20°	991.2
22.5°	940.4
25°	878.0
27.5°	811.1
30°	725.6
32.5°	623.8
35°	522.2
37.5°	429.8
40°	348.9
42.5°	286.5
45°	240.4
47.5°	203.3
50°	177.9
52.5°	157.2
55°	140.9
57.5°	124.8
60°	108.6
62.5°	97.1
65°	83.2
67.5°	71.7
70°	60.1
72.5°	50.8
75°	41.6
77.5°	32.4
80°	23.1
82.5°	16.1
85°	9.3
87.5°	2.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)