

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211754

Luminaire Tested: **LE\_4B20D010 EC4B10209040 4LBW1GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211754  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B20D010 EC4B10209040 4LBW1GPH  
Description: PORTFOLIO 4 INCH CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1333.7 lumens  
Efficiency: N/A  
Efficacy: 64.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211754

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBW1GPH

### Luminous Intensity Polar Plot






TEST NUMBER: P211754

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBW1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211754

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBW1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.5	6.8
10°-20°	256.6	19.2
20°-30°	368.0	27.6
30°-40°	346.5	26.0
40°-50°	191.4	14.3
50°-60°	61.4	4.6
60°-70°	15.4	1.2
70°-80°	3.6	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.2	53.6
0°-40°	1061.7	79.6
0°-60°	1314.4	98.6
0°-90°	1333.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1333.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	960	
5°	955	91
15°	909	257
25°	807	368
35°	562	347
45°	243	191
55°	62	61
65°	14	15
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P211754

CATALOG NUMBER: LE\_4B20D010 EC4B10209040 4LBW1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	960.0
2.5°	953.1
5°	955.4
7.5°	948.4
10°	936.8
12.5°	925.2
15°	909.1
17.5°	895.2
20°	872.1
22.5°	839.7
25°	807.2
27.5°	763.4
30°	705.5
32.5°	640.8
35°	562.1
37.5°	478.8
40°	393.2
42.5°	314.6
45°	242.9
47.5°	182.7
50°	131.9
52.5°	92.6
55°	62.4
57.5°	41.6
60°	30.0
62.5°	20.8
65°	13.9
67.5°	9.3
70°	7.0
72.5°	4.6
75°	2.3
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)