

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211764

Luminaire Tested: **LE_4B20D010 EC4B10208050 4LBM1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10208050 4LBM1H
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1829.1 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211764
CATALOG NUMBER: LE_4B20D010 EC4B10208050 4LBM1H

Luminous Intensity Polar Plot





TEST NUMBER: P211764

CATALOG NUMBER: LE_4B20D010 EC4B10208050 4LBM1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211764

CATALOG NUMBER: LE_4B20D010 EC4B10208050 4LBM1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.9	9.1
10°-20°	437.8	23.9
20°-30°	562.6	30.8
30°-40°	423.3	23.1
40°-50°	170.0	9.3
50°-60°	48.3	2.6
60°-70°	15.3	0.8
70°-80°	4.4	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.4	63.8
0°-40°	1590.7	87.0
0°-60°	1809.0	98.9
0°-90°	1829.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1829.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1814	
5°	1781	167
15°	1562	438
25°	1242	563
35°	679	423
45°	210	170
55°	50	48
65°	14	15
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P211764

CATALOG NUMBER: LE_4B20D010 EC4B10208050 4LBM1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1813.7
2.5°	1802.6
5°	1780.6
7.5°	1739.2
10°	1686.6
12.5°	1623.2
15°	1562.5
17.5°	1493.5
20°	1418.9
22.5°	1338.9
25°	1242.2
27.5°	1126.2
30°	991.0
32.5°	839.3
35°	679.1
37.5°	530.0
40°	397.5
42.5°	292.7
45°	209.8
47.5°	143.5
50°	99.4
52.5°	69.0
55°	49.6
57.5°	35.8
60°	27.6
62.5°	19.4
65°	13.8
67.5°	11.0
70°	8.2
72.5°	5.6
75°	2.8
77.5°	2.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)