

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211793

Luminaire Tested: **LE_4B20D010 EC4B10209050 4LBM1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209050 4LBM1H
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1539.4 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211793
CATALOG NUMBER: LE_4B20D010 EC4B10209050 4LBM1H

Luminous Intensity Polar Plot





TEST NUMBER: P211793

CATALOG NUMBER: LE_4B20D010 EC4B10209050 4LBM1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211793

CATALOG NUMBER: LE_4B20D010 EC4B10209050 4LBM1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	9.1
10°-20°	368.5	23.9
20°-30°	473.6	30.8
30°-40°	356.3	23.1
40°-50°	143.1	9.3
50°-60°	40.7	2.6
60°-70°	12.9	0.8
70°-80°	3.6	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.6	63.8
0°-40°	1338.9	87.0
0°-60°	1522.6	98.9
0°-90°	1539.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1539.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1527	
5°	1499	140
15°	1315	369
25°	1046	474
35°	572	356
45°	177	143
55°	42	41
65°	12	13
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P211793

CATALOG NUMBER: LE_4B20D010 EC4B10209050 4LBM1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1526.6
2.5°	1517.3
5°	1498.7
7.5°	1463.8
10°	1419.6
12.5°	1366.2
15°	1315.1
17.5°	1257.0
20°	1194.3
22.5°	1126.9
25°	1045.6
27.5°	948.0
30°	834.2
32.5°	706.3
35°	571.5
37.5°	446.1
40°	334.5
42.5°	246.3
45°	176.6
47.5°	120.9
50°	83.6
52.5°	58.1
55°	41.9
57.5°	30.2
60°	23.2
62.5°	16.2
65°	11.6
67.5°	9.3
70°	7.0
72.5°	4.6
75°	2.3
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)