

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778360

Luminaire Tested: LERS4D15D010-EC4DR400215IC9035-4LBS1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P778360  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LERS4D15D010-EC4DR400215IC9035-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1463.0 lumens  
Efficiency: N/A  
Efficacy: 92.6 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P778360  
CATALOG NUMBER: LERS4D15D010-EC4DR400215IC9035-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P778360

CATALOG NUMBER: LERS4D15D010-EC4DR400215IC9035-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96									96																		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88									88																		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84									84																		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81									81																		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77									77																		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74									74																		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72									72																		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69									69																		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67									67																		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	372164
5°	370350
10°	350058
15°	297594
20°	202838
25°	84630
30°	26608
35°	12365
40°	6846
45°	3137
50°	1513
55°	838
60°	437
65°	155
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3137 cd/sqm



TEST NUMBER: P778360

CATALOG NUMBER: LERS4D15D010-EC4DR400215IC9035-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	315.3	21.6
10°-20°	706.4	48.3
20°-30°	353.6	24.2
30°-40°	64.8	4.4
40°-50°	17.9	1.2
50°-60°	4.2	0.3
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.2	94.0
0°-40°	1440.0	98.4
0°-60°	1462.1	99.9
0°-90°	1463.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1463.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3406	
5°	3377	315
15°	2631	706
25°	702	354
35°	93	65
45°	20	18
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778360

CATALOG NUMBER: LERS4D15D010-EC4DR400215IC9035-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3406.2
2.5°	3401.2
5°	3376.7
7.5°	3298.7
10°	3155.2
12.5°	2931.6
15°	2630.9
17.5°	2240.0
20°	1744.5
22.5°	1189.3
25°	702.0
27.5°	371.1
30°	210.9
32.5°	136.3
35°	92.7
37.5°	66.2
40°	48.0
42.5°	32.8
45°	20.3
47.5°	12.9
50°	8.9
52.5°	6.4
55°	4.4
57.5°	2.8
60°	2.0
62.5°	1.2
65°	0.6
67.5°	0.4
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)