

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211828

Luminaire Tested: **LE_4B30D010 EC4B30509024 4LBN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509024 4LBN1H
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1528.8 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211828

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBN1H

Luminous Intensity Polar Plot





TEST NUMBER: P211828

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	76	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211828

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.2	11.3
10°-20°	420.1	27.5
20°-30°	487.7	31.9
30°-40°	323.0	21.1
40°-50°	90.6	5.9
50°-60°	22.8	1.5
60°-70°	8.6	0.6
70°-80°	2.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.0	70.7
0°-40°	1403.9	91.8
0°-60°	1517.3	99.2
0°-90°	1528.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1528.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1919	
5°	1870	173
15°	1504	420
25°	1069	488
35°	518	323
45°	105	91
55°	25	23
65°	8	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P211828

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1919.3
2.5°	1911.1
5°	1869.6
7.5°	1797.5
10°	1708.9
12.5°	1609.2
15°	1503.9
17.5°	1401.5
20°	1287.9
22.5°	1182.6
25°	1069.1
27.5°	961.1
30°	822.6
32.5°	675.8
35°	517.9
37.5°	371.1
40°	252.1
42.5°	163.4
45°	105.2
47.5°	63.7
50°	41.5
52.5°	30.5
55°	24.9
57.5°	19.4
60°	13.8
62.5°	11.1
65°	8.4
67.5°	5.6
70°	5.6
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)