

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211835

Luminaire Tested: **LE_4B30D010 EC4B30509024 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509024 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2402.3 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211835

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P211835

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77				77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51				51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34				34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211835

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.7	4.9
10°-20°	319.9	13.3
20°-30°	444.2	18.5
30°-40°	484.8	20.2
40°-50°	452.2	18.8
50°-60°	343.2	14.3
60°-70°	188.0	7.8
70°-80°	51.7	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	881.8	36.7
0°-40°	1366.5	56.9
0°-60°	2162.0	90.0
0°-90°	2402.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2402.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1256	
5°	1246	118
15°	1140	320
25°	966	444
35°	775	485
45°	587	452
55°	384	343
65°	188	188
75°	45	52
85°	0	1
90°	0	



TEST NUMBER: P211835

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1256.4
2.5°	1256.4
5°	1245.8
7.5°	1229.9
10°	1206.2
12.5°	1174.4
15°	1140.0
17.5°	1097.7
20°	1058.0
22.5°	1010.5
25°	965.5
27.5°	920.5
30°	870.2
32.5°	822.7
35°	775.0
37.5°	727.4
40°	682.4
42.5°	634.9
45°	587.2
47.5°	539.6
50°	486.7
52.5°	436.4
55°	383.5
57.5°	333.3
60°	283.0
62.5°	232.8
65°	187.8
67.5°	145.5
70°	108.5
72.5°	74.0
75°	45.0
77.5°	21.1
80°	5.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)