

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211837

Luminaire Tested: **LE_4B30D010 EC4B30509024 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509024 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2505.3 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211837

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211837

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211837

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	3.8
10°-20°	272.6	10.9
20°-30°	410.6	16.4
30°-40°	488.6	19.5
40°-50°	487.7	19.5
50°-60°	396.6	15.8
60°-70°	244.0	9.7
70°-80°	94.5	3.8
80°-90°	15.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	778.9	31.1
0°-40°	1267.4	50.6
0°-60°	2151.7	85.9
0°-90°	2505.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2505.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1009	
5°	1006	96
15°	968	273
25°	894	411
35°	782	489
45°	634	488
55°	444	397
65°	245	244
75°	86	95
85°	12	15
90°	0	



TEST NUMBER: P211837

CATALOG NUMBER: LE_4B30D010 EC4B30509024 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1009.4
2.5°	1010.9
5°	1006.4
7.5°	1000.5
10°	993.1
12.5°	979.7
15°	967.9
17.5°	950.0
20°	930.8
22.5°	912.9
25°	893.7
27.5°	866.9
30°	840.2
32.5°	814.9
35°	782.3
37.5°	746.7
40°	714.0
42.5°	674.0
45°	633.8
47.5°	590.8
50°	544.7
52.5°	497.3
55°	443.8
57.5°	391.8
60°	341.4
62.5°	292.4
65°	244.9
67.5°	200.4
70°	158.8
72.5°	120.3
75°	86.1
77.5°	56.4
80°	34.1
82.5°	20.8
85°	11.8
87.5°	5.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)