

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211857

Luminaire Tested: **LE\_4B30D010 EC4B30508027 4LBN1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211857  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LE\_4B30D010 EC4B30508027 4LBN1H  
Description: PORTFOLIO 4 INCH CYLINDER  
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2023.7 lumens  
Efficiency: N/A  
Efficacy: 72.3 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211857

CATALOG NUMBER: LE\_4B30D010 EC4B30508027 4LBN1H

### Luminous Intensity Polar Plot





TEST NUMBER: P211857

CATALOG NUMBER: LE\_4B30D010 EC4B30508027 4LBN1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P211857

CATALOG NUMBER: LE\_4B30D010 EC4B30508027 4LBN1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.2	11.3
10°-20°	556.1	27.5
20°-30°	645.6	31.9
30°-40°	427.5	21.1
40°-50°	119.9	5.9
50°-60°	30.1	1.5
60°-70°	11.3	0.6
70°-80°	3.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1431.0	70.7
0°-40°	1858.5	91.8
0°-60°	2008.5	99.3
0°-90°	2023.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2023.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2541	
5°	2475	229
15°	1991	556
25°	1415	646
35°	686	428
45°	139	120
55°	33	30
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P211857

CATALOG NUMBER: LE\_4B30D010 EC4B30508027 4LBN1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2540.9
2.5°	2529.8
5°	2474.9
7.5°	2379.5
10°	2262.2
12.5°	2130.2
15°	1990.9
17.5°	1855.2
20°	1704.9
22.5°	1565.5
25°	1415.3
27.5°	1272.3
30°	1088.9
32.5°	894.6
35°	685.7
37.5°	491.3
40°	333.6
42.5°	216.3
45°	139.3
47.5°	84.3
50°	55.0
52.5°	40.4
55°	32.9
57.5°	25.6
60°	18.3
62.5°	14.6
65°	11.0
67.5°	7.3
70°	7.3
72.5°	3.7
75°	3.7
77.5°	3.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)