

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211864

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBS1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBS1H
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3180.1 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211864

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P211864

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77				77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67				67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58				58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51				51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34				34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31				31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211864

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	4.9
10°-20°	423.4	13.3
20°-30°	588.1	18.5
30°-40°	641.7	20.2
40°-50°	598.6	18.8
50°-60°	454.4	14.3
60°-70°	248.8	7.8
70°-80°	68.4	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1167.3	36.7
0°-40°	1809.0	56.9
0°-60°	2862.0	90.0
0°-90°	3180.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3180.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1663	
5°	1649	156
15°	1509	423
25°	1278	588
35°	1026	642
45°	777	599
55°	508	454
65°	249	249
75°	60	68
85°	0	1
90°	0	



TEST NUMBER: P211864

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1663.2
2.5°	1663.2
5°	1649.2
7.5°	1628.2
10°	1596.7
12.5°	1554.6
15°	1509.2
17.5°	1453.1
20°	1400.6
22.5°	1337.6
25°	1278.1
27.5°	1218.6
30°	1152.0
32.5°	1089.0
35°	1025.9
37.5°	962.9
40°	903.4
42.5°	840.4
45°	777.3
47.5°	714.3
50°	644.3
52.5°	577.8
55°	507.7
57.5°	441.1
60°	374.7
62.5°	308.1
65°	248.6
67.5°	192.6
70°	143.6
72.5°	98.0
75°	59.5
77.5°	28.0
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)