

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211866

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3316.6 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211866

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211866

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 110 | 106 | 102 | 99 | 107 | 104 | 100 | 97 | 99 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 88 | 86 | | | | | | | | | | | | | | | | | | | |
| 2 | 101 | 93 | 87 | 82 | 98 | 92 | 86 | 81 | 88 | 83 | 79 | 85 | 81 | 77 | 82 | 79 | 76 | 74 | | | | | | | | | | | | | | | | | | | |
| 3 | 93 | 83 | 75 | 69 | 90 | 81 | 74 | 69 | 78 | 72 | 67 | 76 | 70 | 66 | 73 | 69 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 4 | 85 | 74 | 65 | 59 | 83 | 72 | 65 | 59 | 70 | 63 | 58 | 68 | 62 | 57 | 66 | 61 | 56 | 54 | | | | | | | | | | | | | | | | | | | |
| 5 | 78 | 66 | 58 | 51 | 76 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 59 | 54 | 49 | 47 | | | | | | | | | | | | | | | | | | | |
| 6 | 73 | 60 | 51 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 44 | 55 | 49 | 44 | 54 | 48 | 44 | 42 | | | | | | | | | | | | | | | | | | | |
| 7 | 67 | 54 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 39 | 49 | 43 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 8 | 63 | 50 | 41 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 35 | 46 | 40 | 35 | 45 | 39 | 35 | 33 | | | | | | | | | | | | | | | | | | | |
| 9 | 59 | 46 | 38 | 32 | 57 | 45 | 37 | 32 | 44 | 37 | 32 | 43 | 36 | 32 | 42 | 36 | 32 | 30 | | | | | | | | | | | | | | | | | | | |
| 10 | 55 | 42 | 34 | 29 | 54 | 42 | 34 | 29 | 41 | 34 | 29 | 40 | 33 | 29 | 39 | 33 | 29 | 27 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211866

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 126.6 | 3.8 |
| 10°-20° | 360.9 | 10.9 |
| 20°-30° | 543.5 | 16.4 |
| 30°-40° | 646.7 | 19.5 |
| 40°-50° | 645.6 | 19.5 |
| 50°-60° | 525.0 | 15.8 |
| 60°-70° | 323.0 | 9.7 |
| 70°-80° | 125.2 | 3.8 |
| 80°-90° | 20.1 | 0.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1031.1 | 31.1 |
| 0°-40° | 1677.8 | 50.6 |
| 0°-60° | 2848.4 | 85.9 |
| 0°-90° | 3316.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3316.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1336 | |
| 5° | 1332 | 127 |
| 15° | 1281 | 361 |
| 25° | 1183 | 544 |
| 35° | 1036 | 647 |
| 45° | 839 | 646 |
| 55° | 588 | 525 |
| 65° | 324 | 323 |
| 75° | 114 | 125 |
| 85° | 16 | 20 |
| 90° | 0 | |



TEST NUMBER: P211866

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1MW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1336.2 |
| 2.5° | 1338.2 |
| 5° | 1332.4 |
| 7.5° | 1324.5 |
| 10° | 1314.6 |
| 12.5° | 1297.0 |
| 15° | 1281.2 |
| 17.5° | 1257.7 |
| 20° | 1232.2 |
| 22.5° | 1208.5 |
| 25° | 1183.0 |
| 27.5° | 1147.6 |
| 30° | 1112.2 |
| 32.5° | 1078.8 |
| 35° | 1035.6 |
| 37.5° | 988.4 |
| 40° | 945.2 |
| 42.5° | 892.2 |
| 45° | 839.1 |
| 47.5° | 782.1 |
| 50° | 721.2 |
| 52.5° | 658.3 |
| 55° | 587.5 |
| 57.5° | 518.8 |
| 60° | 451.9 |
| 62.5° | 387.1 |
| 65° | 324.2 |
| 67.5° | 265.3 |
| 70° | 210.3 |
| 72.5° | 159.2 |
| 75° | 114.0 |
| 77.5° | 74.7 |
| 80° | 45.2 |
| 82.5° | 27.5 |
| 85° | 15.8 |
| 87.5° | 7.9 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)