

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211868

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBS1WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBS1WMH
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3224.3 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211868

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P211868

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70		
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62		
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56		
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50		
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45		
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38		
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211868

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.9	5.9
10°-20°	500.5	15.5
20°-30°	672.2	20.8
30°-40°	688.1	21.3
40°-50°	595.6	18.5
50°-60°	396.1	12.3
60°-70°	162.7	5.0
70°-80°	19.3	0.6
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1361.6	42.2
0°-40°	2049.6	63.6
0°-60°	3041.4	94.3
0°-90°	3224.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3224.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2044	
5°	2012	189
15°	1788	501
25°	1467	672
35°	1099	688
45°	776	596
55°	440	396
65°	161	163
75°	8	19
85°	0	1
90°	0	



TEST NUMBER: P211868

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBS1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2043.6
2.5°	2039.3
5°	2011.8
7.5°	1969.6
10°	1912.5
12.5°	1849.0
15°	1787.8
17.5°	1709.6
20°	1633.5
22.5°	1553.2
25°	1466.6
27.5°	1373.7
30°	1280.6
32.5°	1187.6
35°	1098.9
37.5°	1014.4
40°	934.0
42.5°	853.8
45°	775.6
47.5°	693.1
50°	608.7
52.5°	524.1
55°	439.5
57.5°	365.6
60°	289.5
62.5°	219.8
65°	160.7
67.5°	105.7
70°	61.2
72.5°	29.6
75°	8.5
77.5°	4.2
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)