

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211872

Luminaire Tested: **LE_4B30D010 EC4B30508027 4LBW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30508027 4LBW1LI
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3206.4 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211872

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211872

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																			
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77																			
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70																			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58																			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54																			
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49																			
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45																			
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211872

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.1	6.0
10°-20°	606.3	18.9
20°-30°	945.8	29.5
30°-40°	920.3	28.7
40°-50°	459.7	14.3
50°-60°	71.2	2.2
60°-70°	8.6	0.3
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1744.3	54.4
0°-40°	2664.5	83.1
0°-60°	3195.4	99.7
0°-90°	3206.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3206.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1965	
5°	1990	192
15°	2141	606
25°	2078	946
35°	1494	920
45°	576	460
55°	59	71
65°	7	9
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P211872

CATALOG NUMBER: LE_4B30D010 EC4B30508027 4LBW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1964.6
2.5°	1972.0
5°	1990.3
7.5°	2019.7
10°	2056.4
12.5°	2104.1
15°	2140.9
17.5°	2170.2
20°	2174.0
22.5°	2148.2
25°	2078.5
27.5°	1975.6
30°	1847.1
32.5°	1685.5
35°	1494.5
37.5°	1285.3
40°	1064.9
42.5°	829.9
45°	576.5
47.5°	370.9
50°	224.0
52.5°	121.2
55°	58.8
57.5°	25.8
60°	14.7
62.5°	11.0
65°	7.3
67.5°	7.3
70°	3.7
72.5°	3.7
75°	3.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)