

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211876

Luminaire Tested: **LE_4B30D010 EC4B30509027 4LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509027 4LBCS1MMS
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2451.4 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211876

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P211876

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76				76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50				50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44				44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40				40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36				36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32				32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211876

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.1	4.3
10°-20°	297.7	12.1
20°-30°	434.8	17.7
30°-40°	497.3	20.3
40°-50°	478.0	19.5
50°-60°	369.1	15.1
60°-70°	206.0	8.4
70°-80°	59.9	2.4
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.6	34.2
0°-40°	1335.9	54.5
0°-60°	2182.9	89.0
0°-90°	2451.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2451.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1126	
5°	1116	106
15°	1056	298
25°	945	435
35°	796	497
45°	623	478
55°	414	369
65°	206	206
75°	52	60
85°	2	3
90°	0	



TEST NUMBER: P211876

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1125.8
2.5°	1125.8
5°	1116.3
7.5°	1111.5
10°	1095.6
12.5°	1076.6
15°	1055.9
17.5°	1035.4
20°	1005.3
22.5°	981.5
25°	945.1
27.5°	908.5
30°	872.1
32.5°	835.5
35°	796.0
37.5°	756.3
40°	710.4
42.5°	669.1
45°	623.2
47.5°	570.8
50°	521.7
52.5°	467.7
55°	413.9
57.5°	358.3
60°	306.0
62.5°	253.7
65°	206.1
67.5°	161.7
70°	120.5
72.5°	84.0
75°	52.3
77.5°	26.9
80°	9.5
82.5°	3.1
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)