

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210735

Luminaire Tested: **LE_4B10D010 EC4B10208027 4LBS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10208027 4LBS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1220.3 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210735

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P210735

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	107	104	100	97	99	97	94		96	93	91		92
2	101	93	87	82	98	92	86	81	88	83	79		85	81	77		82
3	93	83	75	69	90	81	74	69	78	72	67		76	70	66		73
4	85	74	65	59	83	72	65	59	70	63	58		68	62	57		66
5	78	66	58	51	76	65	57	51	63	56	51		61	55	50		59
6	73	60	51	45	71	59	51	45	57	50	44		55	49	44		54
7	67	54	46	40	66	54	46	40	52	45	40		51	44	39		49
8	63	50	41	36	61	49	41	36	48	41	35		46	40	35		45
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42
10	55	42	34	29	54	42	34	29	41	34	29		40	33	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210735

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	3.8
10°-20°	132.8	10.9
20°-30°	200.0	16.4
30°-40°	238.0	19.5
40°-50°	237.6	19.5
50°-60°	193.2	15.8
60°-70°	118.8	9.7
70°-80°	46.1	3.8
80°-90°	7.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.3	31.1
0°-40°	617.3	50.6
0°-60°	1048.1	85.9
0°-90°	1220.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1220.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	492	
5°	490	47
15°	471	133
25°	435	200
35°	381	238
45°	309	238
55°	216	193
65°	119	119
75°	42	46
85°	6	7
90°	0	



TEST NUMBER: P210735

CATALOG NUMBER: LE_4B10D010 EC4B10208027 4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	491.7
2.5°	492.4
5°	490.2
7.5°	487.3
10°	483.7
12.5°	477.2
15°	471.4
17.5°	462.7
20°	453.3
22.5°	444.6
25°	435.2
27.5°	422.2
30°	409.2
32.5°	397.0
35°	381.1
37.5°	363.7
40°	347.8
42.5°	328.3
45°	308.8
47.5°	287.8
50°	265.4
52.5°	242.2
55°	216.2
57.5°	190.9
60°	166.3
62.5°	142.4
65°	119.2
67.5°	97.6
70°	77.4
72.5°	58.6
75°	42.0
77.5°	27.5
80°	16.6
82.5°	10.1
85°	5.8
87.5°	2.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)