

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211883

Luminaire Tested: **LE_4B30D010 EC4B30509027 4LBM1WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509027 4LBM1WH
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2135.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211883

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBM1WH

Luminous Intensity Polar Plot





TEST NUMBER: P211883

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBM1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211883

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBM1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.3	11.0
10°-20°	602.3	28.2
20°-30°	706.6	33.1
30°-40°	447.2	20.9
40°-50°	119.8	5.6
50°-60°	16.7	0.8
60°-70°	6.2	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1543.1	72.3
0°-40°	1990.3	93.2
0°-60°	2126.8	99.6
0°-90°	2135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2536	
5°	2495	234
15°	2157	602
25°	1561	707
35°	710	447
45°	136	120
55°	16	17
65°	6	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P211883

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBM1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2535.8
2.5°	2526.2
5°	2494.7
7.5°	2444.2
10°	2371.7
12.5°	2277.1
15°	2157.3
17.5°	2034.3
20°	1886.0
22.5°	1734.7
25°	1561.1
27.5°	1371.9
30°	1160.6
32.5°	930.4
35°	709.6
37.5°	514.1
40°	353.2
42.5°	227.1
45°	135.6
47.5°	75.7
50°	40.9
52.5°	22.0
55°	15.8
57.5°	12.6
60°	9.5
62.5°	9.5
65°	6.3
67.5°	3.1
70°	3.1
72.5°	3.1
75°	3.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)