

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211888

Luminaire Tested: **LE_4B30D010 EC4B30509027 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509027 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1983.7 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211888

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBN1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211888

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211888

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.7	7.8
10°-20°	407.3	20.5
20°-30°	536.1	27.0
30°-40°	417.3	21.0
40°-50°	202.7	10.2
50°-60°	128.0	6.5
60°-70°	82.6	4.2
70°-80°	43.2	2.2
80°-90°	10.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1099.1	55.4
0°-40°	1516.5	76.4
0°-60°	1847.2	93.1
0°-90°	1983.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1983.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1692	
5°	1661	156
15°	1453	407
25°	1182	536
35°	668	417
45°	252	203
55°	142	128
65°	82	83
75°	41	43
85°	9	11
90°	0	



TEST NUMBER: P211888

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1692.2
2.5°	1682.8
5°	1660.8
7.5°	1623.0
10°	1572.5
12.5°	1515.8
15°	1452.8
17.5°	1386.5
20°	1317.3
22.5°	1251.1
25°	1181.7
27.5°	1093.5
30°	973.7
32.5°	832.0
35°	668.0
37.5°	516.8
40°	400.2
42.5°	311.9
45°	252.1
47.5°	204.9
50°	179.6
52.5°	160.7
55°	141.8
57.5°	126.1
60°	110.3
62.5°	94.5
65°	81.9
67.5°	72.5
70°	59.9
72.5°	50.5
75°	40.9
77.5°	31.6
80°	22.0
82.5°	15.8
85°	9.4
87.5°	3.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)