

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211899

Luminaire Tested: **LE_4B30D010 EC4B30509027 4LBW1GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509027 4LBW1GPH
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1819.7 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211899

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBW1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P211899

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBW1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92											92																	
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83											83																	
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76											76																	
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69											69																	
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63											63																	
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57											57																	
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53											53																	
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48											48																	
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45											45																	
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41											41																	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211899

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBW1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.5	6.8
10°-20°	350.1	19.2
20°-30°	502.1	27.6
30°-40°	472.8	26.0
40°-50°	261.1	14.3
50°-60°	83.8	4.6
60°-70°	20.9	1.2
70°-80°	4.9	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.7	53.6
0°-40°	1448.5	79.6
0°-60°	1793.4	98.6
0°-90°	1819.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1819.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1310	
5°	1303	124
15°	1240	350
25°	1101	502
35°	767	473
45°	331	261
55°	85	84
65°	19	21
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P211899

CATALOG NUMBER: LE_4B30D010 EC4B30509027 4LBW1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1309.8
2.5°	1300.2
5°	1303.4
7.5°	1294.0
10°	1278.2
12.5°	1262.4
15°	1240.3
17.5°	1221.4
20°	1189.8
22.5°	1145.6
25°	1101.4
27.5°	1041.4
30°	962.6
32.5°	874.2
35°	766.9
37.5°	653.3
40°	536.5
42.5°	429.2
45°	331.4
47.5°	249.3
50°	179.9
52.5°	126.2
55°	85.3
57.5°	56.8
60°	41.1
62.5°	28.4
65°	18.9
67.5°	12.6
70°	9.5
72.5°	6.3
75°	3.1
77.5°	3.1
80°	3.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)