

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210755

Luminaire Tested: **LE_4B10D010 EC4B10209027 4LBN1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35178)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209027 4LBN1H
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 640.3 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210755

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBN1H

Luminous Intensity Polar Plot





TEST NUMBER: P210755

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBN1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87835
5°	85878
10°	79404
15°	71251
20°	62718
25°	53985
30°	43463
35°	28931
40°	15062
45°	6814
50°	2958
55°	1981
60°	1267
65°	905
70°	735
75°	507
80°	0
85°	0



TEST NUMBER: P210755

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBN1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	11.3
10°-20°	175.9	27.5
20°-30°	204.3	31.9
30°-40°	135.3	21.1
40°-50°	37.9	5.9
50°-60°	9.5	1.5
60°-70°	3.6	0.6
70°-80°	1.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.7	70.7
0°-40°	588.0	91.8
0°-60°	635.5	99.2
0°-90°	640.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	640.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	804	
5°	783	73
15°	630	176
25°	448	204
35°	217	135
45°	44	38
55°	10	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210755

CATALOG NUMBER: LE_4B10D010 EC4B10209027 4LBN1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	803.9
2.5°	800.4
5°	783.0
7.5°	752.8
10°	715.7
12.5°	674.0
15°	629.9
17.5°	587.0
20°	539.4
22.5°	495.3
25°	447.8
27.5°	402.5
30°	344.5
32.5°	283.0
35°	216.9
37.5°	155.4
40°	105.6
42.5°	68.4
45°	44.1
47.5°	26.7
50°	17.4
52.5°	12.8
55°	10.4
57.5°	8.1
60°	5.8
62.5°	4.6
65°	3.5
67.5°	2.3
70°	2.3
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)