

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211906

Luminaire Tested: **LE_4B30D010 EC4B30509727 4LBCS1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509727 4LBCS1MW
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3533.2 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211906

CATALOG NUMBER: LE_4B30D010 EC4B30509727 4LBCS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P211906

CATALOG NUMBER: LE_4B30D010 EC4B30509727 4LBCS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211906

CATALOG NUMBER: LE_4B30D010 EC4B30509727 4LBCS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.7	3.9
10°-20°	389.3	11.0
20°-30°	585.6	16.6
30°-40°	694.0	19.6
40°-50°	690.6	19.5
50°-60°	556.7	15.8
60°-70°	336.8	9.5
70°-80°	125.0	3.5
80°-90°	18.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1111.5	31.5
0°-40°	1805.5	51.1
0°-60°	3052.8	86.4
0°-90°	3533.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3533.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1443	
5°	1437	137
15°	1379	389
25°	1272	586
35°	1111	694
45°	899	691
55°	621	557
65°	338	337
75°	113	125
85°	15	19
90°	0	



TEST NUMBER: P211906

CATALOG NUMBER: LE_4B30D010 EC4B30509727 4LBCS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1443.2
2.5°	1443.2
5°	1436.7
7.5°	1432.4
10°	1419.6
12.5°	1398.1
15°	1378.9
17.5°	1357.4
20°	1331.8
22.5°	1306.0
25°	1271.8
27.5°	1235.4
30°	1194.8
32.5°	1156.2
35°	1111.3
37.5°	1064.2
40°	1008.5
42.5°	954.9
45°	899.2
47.5°	837.2
50°	768.6
52.5°	698.0
55°	620.9
57.5°	552.4
60°	475.4
62.5°	406.8
65°	338.3
67.5°	274.1
70°	214.1
72.5°	160.5
75°	113.4
77.5°	72.8
80°	42.8
82.5°	25.6
85°	15.0
87.5°	6.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)