

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210778

Luminaire Tested: **LE_4B10D010 EC4B10209727 4LBM1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B10D010 EC4B10209727 4LBM1H
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 668.8 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210778

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBM1H

Luminous Intensity Polar Plot





TEST NUMBER: P210778

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBM1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79				79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73				73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67				67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62				62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47				47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210778

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBM1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	9.1
10°-20°	160.1	23.9
20°-30°	205.7	30.8
30°-40°	154.8	23.1
40°-50°	62.2	9.3
50°-60°	17.7	2.6
60°-70°	5.6	0.8
70°-80°	1.6	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.9	63.8
0°-40°	581.7	87.0
0°-60°	661.5	98.9
0°-90°	668.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	668.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	663	
5°	651	61
15°	571	160
25°	454	206
35°	248	155
45°	77	62
55°	18	18
65°	5	6
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P210778

CATALOG NUMBER: LE_4B10D010 EC4B10209727 4LBM1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	663.2
2.5°	659.1
5°	651.1
7.5°	635.9
10°	616.8
12.5°	593.6
15°	571.3
17.5°	546.1
20°	518.9
22.5°	489.5
25°	454.3
27.5°	411.8
30°	362.4
32.5°	306.8
35°	248.4
37.5°	193.8
40°	145.3
42.5°	107.0
45°	76.7
47.5°	52.5
50°	36.3
52.5°	25.3
55°	18.2
57.5°	13.1
60°	10.1
62.5°	7.1
65°	5.1
67.5°	4.1
70°	3.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)