

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211968

Luminaire Tested: **LE_4B30D010 EC4B30509030 4LBM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509030 4LBM1LI
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2711.7 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211968

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211968

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211968

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.1	14.3
10°-20°	865.3	31.9
20°-30°	860.3	31.7
30°-40°	468.5	17.3
40°-50°	108.3	4.0
50°-60°	15.3	0.6
60°-70°	5.7	0.2
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2112.8	77.9
0°-40°	2581.3	95.2
0°-60°	2704.8	99.7
0°-90°	2711.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2711.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4275	
5°	4186	387
15°	3123	865
25°	1886	860
35°	725	469
45°	125	108
55°	16	15
65°	7	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P211968

CATALOG NUMBER: LE_4B30D010 EC4B30509030 4LBM1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4274.9
2.5°	4265.1
5°	4186.4
7.5°	4025.7
10°	3802.6
12.5°	3474.4
15°	3123.4
17.5°	2775.6
20°	2434.4
22.5°	2155.5
25°	1886.5
27.5°	1630.6
30°	1341.9
32.5°	1020.3
35°	725.1
37.5°	488.8
40°	318.2
42.5°	200.1
45°	124.7
47.5°	72.2
50°	36.1
52.5°	19.7
55°	16.4
57.5°	9.9
60°	9.9
62.5°	6.6
65°	6.6
67.5°	3.2
70°	3.2
72.5°	3.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)